




Recessed Top Track Flush Walk-on Lid

Technical Information

Pool cover track has a radius where it extends into the cover housing as shown in photos below. This must be a smooth radius transition from the deck level to the underside of the Walk-on Lid tray. A 4 inch opening (minimum) must be left between the front of the tray and the housing for the cover to move through as it is moved off of the pool.



The Walk-on Lid tray suggested thickness is 1 inch.
Notice the finished lid end detail and the lid position as shown in photos below.



Note: Each application is going to be different when doing top track with flush Walk-on Lids. These instructions are for reference only. Specific lid tray sizes are the responsibility of the builder. This type of lid can also be done with universal top track.